

KODAK INDUSTRIAL X-RAY FILM 7200

NON-DESTRUCTIVE TESTING

Your Advance Warning System. Move Forward. Confidently.

Kodak's Industrial X-Ray Film 7200 is uniquely qualified for the NDT Industry, with:

- Clean image tone and low noise. Impeccable detail. In short, a sharp, clear image every single time.
- Consistent production quality: ISO9001-2015. Achieved through disciplined manufacturing.
- Durable. Static resistant. Heat resistant. Sturdy. Fewer artifacts. Even under pressure.
- Competitively priced: You won't believe how well our films fit your budget.

The T-Grain Emulsion Advantage

The Kodak Industrial X-Ray Film 7200 incorporates Kodak's patented T-GRAIN Emulsion technology. It's state of the art, specifically designed for industrial radiographic testing applications. Our ASTM E 1815-18 Class I high-speed film offers very fine grain exceptionally high contrast and definition, great for high temperature and static artifact-resistant applications. And its versatility allows you to have direct x-ray or intensification screen options. So that it works best for what you need.

When you have a critical radiography application, our film is the best tool in your toolkit.

Recommended Applications

KODAK Industrial X-Ray Film 7200 comes in a variety of sizes and packaging formats, ideal for:

- Aerospace and aircraft industry
- · Archeologics, Paintings, Sculptures
- · Composite materials
- · Defense and nuclear industry
- Electrical Components
- Forensics
- Forestry
- · Oil and Gas Pipelines
- Tires
- · Welds and Casting

Multiple Film Loads. Extended Imaging Range. Extreme Environments.



KODAK INDUSTRIAL X-RAY FILM 7200

NON-DESTRUCTIVE TESTING

Processing options

Manually or automatically processed in a range of processing cycles. Your options:

Automatic processing

Be aware of precautionary information on product labels and SDS. Exposure conditions: 200 keV ISO/ANSI/EN, KODAK Industrial X-ray Developer Replenisher.

Film characteristics (Sensitometric)

Processors/Cycles	Base + Fog	Relative Exposure ¹	Contrast ²
8 min 79°F (26°C)	0.23	1	4.7

¹⁸ min 79°F (26°C) automatic cycle is assigned a relative exposure of 1

Manual processing

Be aware of precautionary information on product labels and SDS. Develop with rack and tank, using properly replenished solutions.

Developer	Temperature	Time	Agitation
Kodak Industrial X-ray Developer	75°F (24°C)	4 min	5 seconds every 30 seconds



Next?

Visit: www.kodak.com/go/ndtproducts Connect: ndtproducts@kodak.com

Eastman Kodak Company 343 State Street Rochester, NY 14650 USA +1-866-563-2533 in North America. Produced using Kodak Technology. ©Kodak, 2019. Kodak and the Kodak Logo are trademarks of Kodak. Subject to technical change without notice. 190424



Automatic processing

LOG H EXPOSURE (Grays)

-2.40

-1.90

Exposure: 200 keV Direct X-ray with lead screens Processing: Kodak Industrial X-ray chemicals


-2.90

Densitometry: Diffuse Visual

-3.40

1.00 0.00 -3.90

Manual processing



Exposure: 200 kEv Direct X-ray with lead screens **Processing:** Manual Processing 4 minutes @ 75°F

Densitometry: Diffuse Visual



²Contrast is calculated between net densities of 1.5 and 3.0